

CODES FOR ONLINE ORDERING:

LENS MATERIALS:

AIR Airwear Polycarbonate
CL6 Corning Hi-Index 1.60 Glass Clear
G Glass Crown 1.52
H52 Mid-Index Plastic Colormatic
H53 Poly Trilogy Trivex 1.53
H54 Mid-Index 1.54 Spectralite Plastic
H55 Mid-Index Plastic 1.55
H56 Mid-Index Plastic 1.56
H57 Mid-Index Plastic 1.57
H58 Mid-Index Plastic 1.58
H60 Hi-Index Plastic 1.60
H66 Hi-Index Plastic 1.66 Aspheric
H67 Hi-Index Plastic 1.67 Aspheric
H70 High Index Plastic 1.70
H74 High Index Plastic 1.74
HL6 Glass Hi-Index 1.60
HLT Glass Hi-Index 1.70
I56 Instashades 1.56
I60 Instashades 1.60
IN8 Glass Hi-Index 1.80
IPY Instashades Polycarbonate
K56 Kodak Mid-Index 1.56
P Plastic
P53 Phoenix 1.53
P56 Kaenon Polarized 1.56
P60 Polarized Hi-Index 1.60 (Progressive)
P57 Polarized Mid-Index 1.57
P67 Polarized Hi-Index 1.67 Aspheric
PAP Polycarbonate Aspheric Polarized
PL6 Polarized Hi-Index 1.60 (SV)
PLP Polycarbonate Polarized
PLY Polycarbonate
PPC Polycarbonate Photochromic
PR6 Polarized Hi-Index Glass 1.60
PRD Polarized Glass
PRH Polarized Hi-Index
PRM Polarized Mid-Index 1.55
PRY Polarized Plastic
PTD Photo Thin N' Dark Glass 1.52
RCT Reactopol Glass Polarized Changeable
S55 Mid-Index 1.55 Plastic Sungrey
S56 Sunsenors Mid-Index 1.56
SL8 SlimLite Glass Laminated 1.80
SLT SlimLite Glass Laminated 1.70
T53 Transitions Trivex 1.53
T54 Transitions Spectralite 1.54 Mid-Index
T55 Transitions Mid-Index 1.55
T56 Transitions Mid-Index 1.56
T60 Transitions Hi-Index 1.60
T67 Transitions Hi-Index Plastic 1.67 Aspheric
TPH Transitions Mid-Index Polarized
TPR Transitions Polarized
TPX Transitions Phoenix 1.53
TPY Transitions Polycarbonate
TRN Transitions Plastic
XRY X-Ray Glass

LENS COLORS:

A50 Kaenon LTL 50 Aqua
ACE ACE
AGN Apple Green - KBCo
AMB Ambermatic
AMY Aegis Amethyst
ASH SLC IRX Ash
AUT Autumn Gold
AVI PST Avien
BB3 Embassy Blue Blocker
BLA Blue A
BLE Blue
BLU SLC Blue Polaroid
BNC Brown C
BRN VE Photochromic Brown
BTD Brown Thin & Dark
C12 Kaenon LTL 12 Copper
C28 Kaenon LTL 28 Copper
C50 Kaenon LTL 50 Copper
CAR SLC IRX Caramel
CHO SLC IRX Chocolate
CLM Colormatic
CLR Clear
CME Colormatic Extra
COP SLC IRX Copper
CXB Colormatic Extra Brown
CYL Canary Yellow
DID Didymium
DRV Younger Drivewear
EGL PST Eagle
FFM Frost Fire Mirror
FOR SLC IRX Forest
FRF Frost Fire
G12 Kaenon LTL 12 Grey
G15 B & L Grey 3
G28 Kaenon LTL 28 Grey
G31 B & L Grey 2
G60 Grey 60
GLD Aegis Gold
GN1 Green 1
GN2 Green 2
GN3 Green 3
GRN SLC Green Polaroid
GRS SLC IRX Grass
GRY VE Photochromic Grey
GTD Grey Thin & Dark
GVI SLC IRX Grass Violet
GY1 Grey 1
GY2 Grey 2
GY3 Grey 3
GYC Grey C
GYT True Grey - KBCo
HIC Hi Contrast Polaroid
ISB Instashades Brown
ISG Instashades Grey
MEL Melanin
NEB Polaroid Neutral Brown
NEG Polaroid Neautral Grey
NEU Polaroid Neutral
NGT Nighthawk Melanin
NIT Nitevision Hobie
OCN SLC IRX Ocean
ORN Orange Polaroid
PBX Photobrown Extra
PBZ Photobronze
PCB Photocolor Blue
PCG Photocolor Green
PCP Photo Cop Polaroid
PCV Photocolor Violet
PEW Aegis Pewter
PG2 Photogrey 2
PGX Photogrey Extra
PK1 Pink 1
PK2 Pink 2
PK3 Pink 3
PS2 Photosun 2
PUR Purple
RED SLC Red Polaroid
ROS Rose
RSE SLC IRX Rose
SAP Aegis Sapphire
SBL Sky Blue - KBCo
SFL SLC IRX Sunflower
SIT Sitemaster Hobie
SLD Sunlight Dark Grey
SLG Sunmatic Rx Green
SMK SLC IRX Smoke
SSB Sunsenors Brown
SSD Sunlight Super Dark
SSG Sunsenors Grey
SUN SLC IRX Sunset
TAB Beloptix Amber
TAM Beloptix Aquamarine
TBL Beloptix Blue
TBN Transitions Brown
TBU Beloptix Blue
TEA Teal
TGN Transitions Green
TGY Transitions Grey
TN1 Tan 1
TN2 Tan 2
TN3 Tan 3
TOR Beloptix Orange
TPK Beloptix Pink
TPR Beloptix Purple
TRD Beloptix Red
TYL Beloptix Yellow
UNI Unisol
UVG UV Grey 3 Lantz
VIO SLC IRX Violet
Y35 Kaenon LTL 35 Yellow
YEL Yellow

CODES FOR ONLINE ORDERING:

FRONT & BACKSIDE COATINGS:

ACB	Zeiss Advantage AR w/Cool Blue Coating
ACG	Zeiss Advantage AR w/Cool Gold Coating
ACS	Zeiss Advantage AR w/Cool Silver Coating
AGE	Zeiss Advantage Gold AR w/ Tuff Coat
AGT	Zeiss Advantage Gold AR
ASE	Zeiss Advantage Blue AR w/ Tuff Coat
AST	Zeiss Advantage Blue AR
CAG	Zeiss ET Anti-Reflective Coating w/XT Foundation (Gold)
CAR	Zeiss ET Anti-Reflective Coating w/XT Foundation (Blue)
COT	Factory Front Scratch Coat
CRT	Computer Coating (Tint, AR, UV)
CRZ	Crizal Anti-Reflective Coating (Essilor)
CZA	Crizal Alize Anti-Reflective Coating (Essilor)
CZC	Crizal Alize Clear Guard (Essilor)
CZS	Crizal Sun (Essilor)
DAR	Duralux Anti-Reflective (Rodenstock)
EZC	Pech Multi-Layer AR
EZP	EZC
GEP	Zeiss Gold ET
GET	Zeiss Super ET Anti-Reflective Coating (Gold)
HCS	Hoya Clarity Shield
HV	Hoya HiVision
HVV	Hoya HiVision w/ VP
KCL	Kodak Clear AR
NON	Non-tintable Coating
NPP	Nikon Performance Package
PAR	Hoya Premium AR
PC1	Tintable Backside Scratch Coating (1yr)
PC2	Tintable Backside Scratch Coating (2yr)
PTB	Pech Blue AR w/Tuff SRC & Advantage
PTG	Pech Gold AR w/Tuff SRC & Advantage
SAR	Multi-Layer Anit-Reflective Coating
SCL	Seiko Super Clean AR
SEP	Zeiss Super ET
SET	Zeiss Super ET Anti-Reflective Coating (Blue)
SHV	Hoya Super HiVision
SRF	Essilor Reflection Free Anti-Reflective Coating
SUR	Pentax Surpass ECP
TAG	Tuff SAR (Gold)
TAR	Tuff Scratch Coat Non-tintable w/Zeiss AR (Blue or Gold)
TBK	Tiger Back Non-tintable Scratch Coating
TD2	Essilor TD2 Hardcote
TEF	Sola Teflon AR Coating
UAR	Ultraviolet Anti-Reflective Coating
UTM	UTMC Sola Anti-Reflective Coating
UV4	Ultraviolet Plastic Coating
UVG	Ultraviolet Glass Coating
ZXT	Zeiss Foundation Scratch Coating

MIRROR COATINGS:

BMC	Black Mirror
BMX	Baboon Blue Mirror
BVF	Vulture Blue Violet Mirror
CCM	Cougar Copper Mirror
CMC	Colored Mirror
DEM	Dielectric Mirror
DGM	Double Gradient Mirror
DGR	Double Gradient Colored Mirror Glass
FMC	Flash Mirror
GCM	Gradient Colored Mirror
GDF	Giraffe Gold Mirror
GDX	Gorilla Green Mirror
GMC	Gradient Silver Mirror
GRD	Gradient Colored Mirror Glass
MC	Solid Silver Mirror
MCB	Solid Blue Mirror
MCG	Solid Gold Mirror
MET	Metalectic Mirror
MIB	Mira Pol Blue (KBco)
MIG	Mira Pol Green (KBco)
RDX	Rhino Red Mirror
SER	Serengeti
SGD	Serengeti Drivers Gradient
SOL	Solid Color Coating Glass
SVF	Snake Silver Mirror

HELPFUL HINTS FOR REMO

Redo After Dispensing to Patient

- 1) Go to Rx Wizard Archive (*on the Order Look-up screen*)
- 2) Find the job you need to fix (*"Search" can help you find the job*)
- 3) Double click on job
- 4) Go to "Edit Job"
- 5) Answer "Yes" to "Redo Order?"
- 6) Type in reason for redo
- 7) Click on "Save File"
- 8) Click on "Transmit"

Redo After Received from Pech but Before Dispensing

- 1) Go to Order Look-Up
- 2) In-Process Screen (*hasn't been archived yet*)
- 3) Double click on the job
- 4) Click on "Edit Job" and answer "Yes"

In Service Descriptions

- 1) Type what needs to be corrected
- 2) Save
- 3) Go back to Order Look-Up
- 4) Right click on the job
- 5) Mark "Resend"
- 6) Transmit as a normal job